



Direct Reading Cup Tester

CT-1

For determination of CO₂ gas volumes for beverage dispenser

SIMPLY READ CO₂ GAS VOLUME RESULT ON THE DISPLAY AFTER SHAKING.

! EASY OPERATION!

! CONSISTENT RESULT!

! NO PERSON TO PERSON DIFFERENCE!

**! EQUIPPED WITH ACCURATE PRESSURE TRANSDUCER,
THERMO SENSOR, LIGHT WEIGHT PLASTIC BODY!**

AND

!THE SAME USER FRIENDLY FUNCTIONS WITH DGV-1

- 1) No conversion factor is necessary
- 2) A minimum temperature reading is 0.1 °C
- 3) A minimum pressure reading is 0.001 Mpa
- 4) A set of pressure and temperature units can be selected.
- 5) Sensors can be calibrated and adjusted.
- 6) Max. 5 new values can be written and read.
- 7) Altitude correction is possible.

For more Information, please contact:

BQSL Japan Co., Ltd.

5-11-8-102 Okada, Atsugi-shi,

Kanagawa, 243-0021 JAPAN

Tel/Fax: +81-46-230-0417

e-mail: mail@bqsl.co.jp

<http://www.bqsl.co.jp>

“Make your process simple!

High quality is expected

at Lower cost!”